

Básica

Santiago Roqueta,
Equipo Santa & Cole, 1987
Table lamp



(A) Básica M1



(B) Básica M2

Básica M1



A

Básica M2



B

At a time when international preferences were leaning towards lamps with metal shafts and dichroic halogen bulbs (in other words, cool beam and touch), the Básica lamp sought to champion other, warmer alternatives. A wooden column, held up by a heavy metal base with the same diameter, supports a range of shades in different shapes and colours. Although the lamp balances well in this format, an optional, wider base may be placed underneath.









The Básica lamp heralded a revival of natural materials, such as wood, stitched cardboard or ribbons, and provided Santa & Cole with a springboard for international expansion, generating an alternative current in Europe that challenged prevalent tastes. A more familiar, craftsman-like and gentle form of modernity was being advocated.

GENERAL DESCRIPTION

Birch wood column with nickel or bronze base. Stabilizing base with nickel or bronze base (optional).

Electric cable length: 2,25 m / 88.6"

2 lampshade options: Básica M1, Básica M2

 Stitched beige parchment M1, M2	 Terracotta Raw Color ribbon M1
 Natural ribbon M1	 Mustard Raw Color ribbon M1
 Red-amber ribbon M1	 Green Raw Color ribbon M1
 Black ribbon M1	 White linen M1

LIGHT SOURCES

Recommended light sources (adjustable):

LED bulb: 10 W

Compact fluorescent: 11 W

Incandescent: Max. 100 W

E27 - E26

(Max. hgt. 115 mm / 4.5")

Light source not included.

Dimmer included.

Compatible with bulbs of the Energy efficiency class (E.E.C): A++... E.

Suitable only for indoor use. Always use the light source recommended or equivalent.

Input voltage : 100, 120, 230 Vac.
(50 Hz / 60 Hz). According to destination.



SANTA & COLE

APPROXIMATE WEIGHT (unpacked)

1,5 Kg / 3.3 lb

REGULATIONS

CE



IP 20

UNE-EN 60598

UNE-EN 55015

UNE-EN 60529



Non-class 2

Dry location only

UL-153

E-352592

MAINTENANCE

Clean with a smooth cloth. Do not use ammonia, solvents or abrasive cleaning products.

OTHERS

The lamp is delivered in different packages.

The assembly instructions are delivered with the product.

MODELS

